

ONYX® 7" DC / IC Target | MAG.II

Metric Specifications

Construction


Anode	304 Stainless Steel
Cathode Body	OFHC Copper
Insulator	PTFE / CTFE

Cooling Requirements

Flow Rate at Maximum Power	0.16 LPS
Maximum Input Pressure, Open Drain	4 BAR
Maximum Input Temperature	20 °C

Dimensions

A	Consult Factory
B	Consult Factory
C	38.1 mm



General

Magnetic Enhancement	Permanent (NdFeB) Encapsulated
Maximum Temperature	100 °C
Source to Substrate Distance	50.8 mm - 304.8 mm
Weight, Approximate Without Options	Consult Factory

Maximum Sputtering Power *

Cathode Voltage	100 - 1500 Volts
Direct Cooled Mode, DC	9 kW
Direct Cooled Mode, RF	3 kW
Discharge Current	18 Amps
Indirect Cooled Mode, DC	3 kW
Indirect Cooled Mode, RF	1 kW
Operating Pressure	0.5 - 50 mTorr

Mounting, Standard

Power Cable, DC	High Temperature, Single Conductor
Power Cable, RF	Copper Strap
Power Connector, DC	Screw Termination
Power Connector, RF	Screw Termination
Stem, Outer Dimension Tubing	38.1 mm
Water, Outer Dimension Tubing	9.6 mm

Target

Cooling	Direct / Indirect
Diameter	177.8 mm
Form	Circular / Planar
Thickness, Magnetic	Up to 6.4 mm Ni
Thickness, Non-Magnetic	6.4 mm - 12.7 mm

Specifications Disclaimer

- All Angstrom Sciences NdFeB magnets are totally encapsulated and protected from degradation by water.
- All sources are available in external configurations.
- Magnetic material calculations are optimized with Nickel targets.
- * Maximum power for cathode only, a target material's properties, such as, thermal and electrical conductivity may limit the maximum process power level.
- Some custom-engineered and specialty magnetrons may not meet standard specifications.
- Specifications are subject to change without notice.
- Thickness will vary depending upon coercivity of target material.
- Typical performance. Results may vary with process parameters such as pressure, flow rate, target material, and substrate rotation, etc.

Please contact us for specifications regarding your application.

Angstrom Sciences | Call +1-412-469-8466 | www.angstromsciences.com